

TECHNICAL DATA SHEET

Slit Lamp Camera Ophthalmic Equipment

Ophthalmic equipment of the cleft lamp chamber

Model

YSLXD-2ER-L

Microscope Type

Galileo Parallel

Magnifications change way

Drum Three Magnifications

Eyepiece Magnification

12.5x

Total Magnifications

10X 16X 25X

Diopter Adjustment

-5D ~ +5D

Illumination

Three Steps (Stepless Optional)

Slit Width

0-14mm Continuous

Slit Height

1-14mm Continuous

Slit Angle

0°-180° Adjustable

Slit Inclination Angle

5° 10° 15° 20°

Light Spot Diameter

0.2mm,1mm,2mm,5mm,10mm,14mm

Filter

Heat Absorption;Grey;Redfree;Cobalt Blue

Fixation

Red LED

Electrical

Illumination Bulb

German Osram Halogen Tungsten Lamp

Led Lamp (Optional)

Input Voltage

110V/220V($\pm 10\%$)

Input Power

60VA

Diffuse Lens

Yes

Preset Lens

Yes

Laser Interface

Optional

Applanation Tonometer Interface

Yes

Base Movement

X: 100mm ± 3

Y: 75mm ± 3

Z: 30mm ± 3

Base Movement

X: 100mm ± 3

Y: 75mm ± 3

Z: 30mm ± 3

Panama | Central America | Caribbean | CARICOM

Information from the authorized catalog. Confirm configuration, accessories and documentation in the quotation.

Assisted translation: review the manufacturer specifications before purchasing.