



Wellmed Pro | Wellview Universal Group

TECHNICAL DATA SHEET

Vet Anaesthesia Machine YSAV120V2

YSAV120V2 Vet Anaesthesia Machine

- * Smart 9-inch touch screen; integrated anesthesia machine with ventilator, saving labor costs
- * Respiration modes include PCV, VCV, SPONT, DEMO. Just set the weight, other parameters are automatically calculated
- * With Electric PEEP function
- * Animal-specific bellows design to meet the needs of clinical scientific research.
- * The internal battery can be used for more than two hours.
- * Suitable for small animals, Non-breathing circuit (Jackson or Bain's Absorber) is available.
- * Selectatec-bar and quick change vaporizer mounting device.
- * Professional airtight breathing circuit design, provide the stable gas anesthesia, save anesthesia gas consumption, to ensure a clean operating room and laboratory environment.
- * External and reusable soda lime canister, easily watch and replace soda lime.
- * With Oxygen flush function to ensure that clinical anesthesia demand and Oxygen supply demand.
- * Anaesthesia CO2 absorber assembly has no dead angle design, fast anesthesia, short recovery and high precision. The CO2 absorber supports both open loop and closed loop anaesthesia design and provides independent access .
- * Provide a special Pop-Off valve, Occlusion design, it can be connected to the exhaust gas recovery system and provide a continuous 2 cmH2O negative pressure for the reaspirator airbag, reducing valve to prevent pressure to hurt the animal, ensure the animal safety .
- * Provides an accurate oxygen flow meter with a display range of 0 to 5LPM
- * Vaporizer: the output concentration is not affected by the change of flow, pressure and temperature, accurate and reliable, equipped with safety locking device to prevent anesthetic leakage. Isoflurane, sevoflurane and halothane vaporizer are optional.
- * The hard aluminum solid shell is used, and the surface sanding treatment is adopted, so that the cleaning and disinfection are more convenient.
- * Visible inspiration and expiration valve
- * With fresh gas output connector, specifically designed to accommodate low flow

Panama | Central America | Caribbean | CARICOM

Information from the authorized catalog. Confirm configuration, accessories and documentation in the quotation.

Assisted translation: review the manufacturer specifications before purchasing.